

# 500 inner height / (mm) GKA max. 20 m free carrying 120 SLE max. 10 m free carrying (1000)

application range

free carrying length Lf / (m)

#### **GKA** characteristics

The GKA is characterized by the highest stability compared to standard chains, with almost unlimited dimensions and the choice of material.

The interior is custom formed and thus guarantees an optimal cable guiding.

Stay lengths up to 1200 mm are possible.

The bending radius can be created according to customer specifications if required.

#### **Dimensions**

bend radius:	200	to	mm
inner height:	118	to	468 mm
inner width:	100	to	1172 mm
energy chain weight:	25	to	85 kg/m

## Travel

The maximum travel distance is determined by the arrangement and the additional weight (line weight). At normal arrangement maximum travel is double the chain length minus the arc of the chain radius. Support rollers or similar constructive steps can increase this value.

## Travel speed

The standard and the stainless steel type are limited at 1 m/ s. Exceeding this and high dynamic loads caused by eg vibrations need the use of carburated material.

#### Acceleration

The acceleration in principle is not limited. However limits may exist if very long chains and line weights cause extreme tensile forces.

# Service temperature

The operating temperature is -20 ° C up to 600 ° C ( stainless steel -40 ° C up to 600 ° C).

inner width / (mm)

00

#### GKA with aluminum profile

A highly customized and robust design that is used mainly in larger steel chains. The stays are created according to the specifications of the user:



#### **GKR** with rods

Made of stainless steel this energy chain is generally offered for off-shore, since aluminum is not suitable for these applications. The chains can be seperated into different sections by additional stainless steel dividers:



#### GKP with plastic dividers

These stays can be especially used for heavy mechanical engineering. The advantages in comparison to the GKA (aluminum profile) are in the price, the weight and space savings.










## **GKA** DIMENSIONS



GKA	bending radius	Tlg. pitch	а	С	0	р	weight <sup>1)</sup> kg/m
110	as specified (>200)	175	118	150	230	110	25
160	as specified (>250)	225	168	200	300	160	30
210	as specified (>300)	275	218	250	370	210	40
260	as specified (>400)	325	268	300	430	260	45
310	as specified (>450)	375	318	350	500	310	55
360	as specified (>550)	425	368	400	560	360	65
410	as specified (>600)	475	418	450	620	410	75
460	as specified (>700)	525	468	500	680	460	85

<sup>\*1)</sup>weight for stay length 500

The bending radius is freely choosen after consultation. It is advantageous to adjust the bending radius of the chain to achieve a minimal polygon effect.

Stay lengths are available in steps of 1 mm.

The usable interior width is stay length minus 14 mm

Stay types and connectors may vary from those representations. Energy chains GKA are custom made in consultation with the client, usually from drawing. Item numbers are not given for this reason.


For energy chains type GKA chooce the order length as an uneven multiple of the pitch.

order example: max. travel distance 20,9 m, bend radius 800 mm, normal constell	ation
---	-------


G	3KA 460	0 / 800	х	14175	/ 1000 / N/N	acc. drawing
	type	/ radius	Х	length	/staylength / connect	

01/2023 102

103



01/2023



## **GKA** sizes

## **GKA 110**

height 150, width and bending radius as specified

# .GKA 160

height 200, width and bending radius as specified

# **GKA210**

height 250, width and bending radius as specified

#### **GKA 260**

height 300, width and bending radius as specified

#### **GKA310**

height 350, width and bending radius as specified

#### **GKA360**


height 400, width and bending radius as specified

## **GKA410**

height 450, width and bending radius as specified

# **GKA460**

height 500, width and bending radius as specified



Content

Informations

