




HELUKABEL®



 Media Technology

HELUSOUND® 500 PUR **HELUSOUND® 600 FRNC**

The flexible speaker cables

HELUEVENT

HELULIGHT®

HELUSOUND®

HELUSOUND® 500 PUR

The robust solution for medium and high mechanical stresses, as robust, abrasion-resistant and cut resistant. Also suitable for outdoor use.

Properties:

- Sheath material/core isolation: PUR/PVC
- Operating temperature range: -25°C to +80°C

HELUSOUND® 500 PUR 2x1.5 mm²

- Conductor resistance max.: 12.7 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 6.6 mm
- Copper weight: 28.8 kg/km
- Weight: approx. 66.9 kg/km
- Part.-No. 400109



HELUSOUND® 500 PUR 2x2.5 mm²

- Conductor resistance max.: 7.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 7.5 mm
- Copper weight: 48.0 kg/km
- Weight: approx. 98.5 kg/km
- Part.-No. 400110



HELUSOUND® 500 PUR 2x4.0 mm²

- Conductor resistance max.: 4.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 9.4 mm
- Copper weight: 76.8 kg/km
- Weight: approx. 150.2 kg/km
- Part.-No. 400111



HELUSOUND® 500 PUR 4x2.5 mm²

- Conductor resistance max.: 7.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 8.8 mm
- Copper weight: 96.0 kg/km
- Weight: approx. 159.1 kg/km
- Part.-No. 400112



HELUSOUND® 500 PUR 4x4.0 mm²

- Conductor resistance max.: 4.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 11.6 mm
- Copper weight: 153.6 kg/km
- Weight: approx. 253.0 kg/km
- Part.-No. 400113



HELUSOUND® 500 PUR 8x2.5 mm²

- Conductor resistance max.: 7.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 13.5 mm
- Copper weight: 192.0 kg/km
- Weight: approx. 332.1 kg/km
- Part.-No. 400114



HELUSOUND® 500 PUR 8x4.0 mm²

- Conductor resistance max.: 4.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 16.8 mm
- Copper weight: 307.2 kg/km
- Weight: approx. 499.5 kg/km
- Part.-No. 400115



HELUSOUND® 600 FRNC

The safe solution for increasing demands on the security in case of fire, as flame retardant, low smoke, halogen-free, no corrosion damage by released gases and fumes.

Properties:

- Sheath material/core isolation: FRNC/FRNC
- Operating temperature range: -5°C to +70°C

HELUSOUND® 600 FRNC 2x1.5 mm²

- Conductor resistance max.: 12.7 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 6.6 mm
- Copper weight: 28.8 kg/km
- Weight: approx. 77.0 kg/km
- Part.-No. 400116



HELUSOUND® 600 FRNC 2x2.5 mm²

- Conductor resistance max.: 7.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 7.5 mm
- Copper weight: 48.0 kg/km
- Weight: approx. 105.6 kg/km
- Part.-No. 400117



HELUSOUND® 600 FRNC 2x4.0 mm²

- Conductor resistance max.: 4.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 9.4 mm
- Copper weight: 76.8 kg/km
- Weight: approx. 166.9 kg/km
- Part.-No. 400118



HELUSOUND® 600 FRNC 4x2.5 mm²

- Conductor resistance max.: 7.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 8.8 mm
- Copper weight: 96.0 kg/km
- Weight: approx. 161.5 kg/km
- Part.-No. 400119



HELUSOUND® 600 FRNC 4x4.0 mm²

- Conductor resistance max.: 4.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 11.6 mm
- Copper weight: 153.6 kg/km
- Weight: approx. 271.6 kg/km
- Part.-No. 400120



HELUSOUND® 600 FRNC 8x2.5 mm²

- Conductor resistance max.: 7.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 13.5 mm
- Copper weight: 192.0 kg/km
- Weight: approx. 338.6 kg/km
- Part.-No. 400121



HELUSOUND® 600 FRNC 8x4.0 mm²

- Conductor resistance max.: 4.9 Ohm/km
- Min. bending radius for laying.: 33 mm
- Cable external-Ø: approx. 16.8 mm
- Copper weight: 307.2 kg/km
- Weight: approx. 531.5 kg/km
- Part.-No. 400122



Our Products for your stage:

- AES/EBU audio cables
- DMX cables
- Round and multicore loudspeaker cables
- Instrument cables
- Microphone cables
- Video cables
- Camera cables
- Connection equipment
- Power cables
- Custom cables as per your requirements

Fax reply to: +49 7150 9209-5501

What can we do for you?

- ☐ Catalogue Cable & Wires
- ☐ Catalogue Cable Accessories
- ☐ Catalogue Data, Network & Bus Technology
- ☐ Catalogue Media Technology
- ☐ Catalogue Wind Power
- ☐ Brochure Photovoltaic
- ☐ Brochure New Cable Accessories
- ☐ Call back
- ☐ Field visit

Want to order catalogues online?

Simply go to
www.helukabel.de/publication-order



Company

First name, surname

Customer number (if applicable)

Street, No.

Zip, City

Telephone / Fax

E-mail

Your message

☐ **Yes**, please include me in the mailing list for the HELUKABEL® e-mail newsletter.
(please check)

helukabel-group.com