



Order infos Design guidelines







order example: max. travel distance 3 m, bending radius 100 mm, standard arrangement							
SFK 32N / 200	x 1900 / N/N						
type / radius	x length / connectors / arrangement						

32 H

200 / 250

75

110

80

115

80

30,5

106

120

5.3

SFK Characteristics

The chain consists of a rectangular, galvanized steel spiral band and mounted in inner radius is a spring steel band. The SFK offers large usable cross-sections at low external dimensions and optimum line protection. At low cantilever lengths the SFK is ideal for areas with hot chips and sparks.

The temperature range is between -40° and +180° C.

10 LOAD DIAGRAM 8 6 load / (kg/m) 2 0 free carrying length Lf / (m)


SFK Flanges

Flange N

Standard is the low priced flange N, each with four mounting holes.



flange N




Flange A

With countersunk screws, knurled nuts and angles the standard flange N changes to flange A.

order example									
SFK 32N	/ 250	Х	3000	/ AA	/ h				
type	/ radius	Х	length	/ flange	/ arrangement				

flange A




Flange B

Flange B is connected laterally with angles. The holes of standard flanges N are omitted.


order example									
SFK 32N type	/ 250 / radius			/ B B / flange	/ h / arrangement				

flange B



Scoop mount

Scoop mount complements the diversity of the possible connector types.



scoop bracket

