



HELUKABEL®

The smooth surface prevents
to adhere harmful micro
organisms




Cable Accessories

HELUTOP® HT-Clean

**Stainless steel cable gland for
highest requirements to
cleanliness and cleaning**

HELUTOP HT-CLEAN

HELUTOP® HT-Clean Stainless steel cable gland



HELUTOP® HT-Clean

Highest requirements to cleanliness and cleaning.

Application

- Food industry - milk and meat products
- Packaging of food machines
- Beverage industry
- Pharmaceutical industry
- Clean room technology
- Biotechnology
- Chemical Industry

Note

- For tightening from outside you have to use the listed tightening tool
- The cable gland can be assembled with a commercial socket wrench
- Delivery including locknut

Material

Body and counter nut: Stainless steel
1.4305/AISI 303
Strain relief: POM
Grommet: **TPE according to
FDA 21 CFR 177.2600**

Properties


- the smooth surface prevents to adhere harmful micro organisms
- easy, fast and less expensive cleaning because of the smooth surface
- suitable for high pressure steam cleaning
- resistant against chemical cleaning supplies
- no threads are exposed
- high tightness
- no enter from water and dirt from outside
- reliable strain relief due to strain relief element separated from grommet

Technical data

Protection class: IP68 - 5bar, 30 min
according to EN 60529
IP69K according to DIN 40 050-9

Temperature range: -20 °C up to +100 °C;
temporary: -40 °C up to +150 °C

Test standard: EN 50262



HELUTOP Clean


Cable incl. Counter nut	Size metric	Cable-Ø from / to mm	SW A mm	D mm	G mm	D2 mm	D4 mm	H mm	TL mm	Recommended Cap Nm	Counter nut SW L mm	Height mm	Recommended Cap Counter nut Nm
906914	12x1,5	3,0-6,5	14,0	15,6	12,0	7,0	6,8	21,5	6,0	2,5	15,0	2,8	6
906915	16x1,5	5,0-10,0	18,0	20,2	16,0	10,0	10,3	23,0	7,0	4,0	19,0	3,0	9
906916	20x1,5	6,0-12,0	22,0	24,1	20,0	13,0	12,3	27,0	10,0	5,0	24,0	3,5	12
906917	25x1,5	12,0-17,0	28,0	30,1	25,0	17,0	17,3	30,0	14,0	6,0	30,0	4,0	14

HELUTOP Clean-EMV

Cable incl. Counter nut	Size metric	Cable-Ø from / to mm	SW A mm	D mm	G mm	D2 mm	D4 mm	H mm	TL mm	Recommended Cap Nm	Counter nut SW L mm	Height mm	Recommended Cap Counter nut Nm
906918	16x1,5	5,0-10,0	18,0	20,2	16,0	10,0	10,3	23,0	7,0	4,0	19,0	3,0	9
906919	20x1,5	6,0-12,0	22,0	24,1	20,0	13,0	12,3	27,0	10,0	5,0	24,0	3,5	12
906920	25x1,5	12,0-17,0	28,0	30,1	25,0	17,0	17,3	30,0	14,0	6,0	30,0	4,0	14

Tightening Tool

Part-Nr.	Size metric	Spanner size B mm	Spanner size C mm	Height mm
906921	12x1,5	5	7	5
906922	16x1,5	6	10	5
906923	20x1,5	8	13	8
906924	25x1,5	10	17	8



Dimensions and specifications may be changed without prior notice.

helukabel-group.com