

SHIPFLEX 330 cable for drag chain, halogen-free, EMC preferred type, meter marking



new

Technical data

- Special screened drag chain cable
- UL-Style 20233
- **Temperature range**
flexing -40 °C to +80 °C
fixed -40 °C to +80 °C
- **Installation temperature**
minimum -25 °C
- **Nominal voltage**
VDE U₀/U 300/500 V
UL 300 V
- **Insulation resistance**
min. 100 MOhm x km
- **Minimum bending radius**
for permanent bending 7,5x cable ø
- **Coupling resistance**
max. 250 Ohm/km
- **Radiation resistance**
up to 100x10⁶ cJ/kg (up to 100 Mrad)

Cable structure

- Bare copper conductor, extra fine wire to DIN VDE 0295 cl. 6, BS 6360 cl. 6 and IEC 60228 cl. 6
- Special core insulation
- Colored cores to DIN 47100
- Cores stranded in layers with optimal lay-length
- Core wrapping between the layers of stranding
- Braided screening of tinned copper wires, coverage approx. 85 % optional aluminium foil under the screen
- **Full polyurethane** outer sheath to UL std. 1581 Tab. 50227
- Sheath colour grey (RAL 7001)
- with meter marking

Properties

- Flame retardant according to VDE 0482-332-1-2, DIN EN 60332-1-2/ IEC 60332-1 (equivalent DIN VDE 0472 part 804 test method B)
- Halogen free to VDE 0482 part 267/ DIN EN 50267-2-1/ IEC 60754-1 (conforms to DIN VDE 0472 part 815)
- Oil resistant to IEC 60092-350, appendix F
- Behaviour at low temperature at -40 ° to IEC 60092-350, appendix E
- Weather, ozon and UV-resistant
- The materials used in manufacture are cadmium-free and contain no silicone and free from substances harmful to the wetting properties of lacquers

Application

HELUKABEL® SHIPFLEX 330 is a new developed and successfully tested special drag chain cable with overall screening which meets the requirements of the strict standards for application in offshore-areas. For this two-line standard there is a **Lloyds Register approval**. The outer sheath insulation of non-adhesive Polyurethan allows the application in extremely oily and rough environmental conditions. For applications which go beyond standard solutions we recommend that you fill out our especially developed questionnaire for drag chains. Before installation in cable drag chains please read the installation instructions.

EMC=Electromagnetic compatibility

To optimise the EMC features we recommend a large round contact of the copper braiding on both ends.

CE= The product is conformed with the EC Low-Voltage Directive 2006/95/EG.

Part no.	No.cores x cross-sec. mm²	AWG-No.	Outer Ø approx. mm	Cop. weight kg / km	Weight approx. kg / km
19846	2 x 0,25	24	5,0	14,9	38,0
19847	3 x 0,25	24	5,2	18,8	44,0
19848	4 x 0,25	24	5,5	21,3	51,0
19849	5 x 0,25	24	5,8	31,0	68,0
19850	7 x 0,25	24	6,7	39,6	82,0
19851	12 x 0,25	24	8,0	59,1	124,0
19852	18 x 0,25	24	9,0	78,4	150,0
19853	25 x 0,25	24	10,8	101,0	204,0
19854	36 x 0,25	24	11,5	126,4	230,0

Part no.	No.cores x cross-sec. mm²	AWG-No.	Outer Ø approx. mm	Cop. weight kg / km	Weight approx. kg / km
19855	2 x 0,34	22	5,2	18,1	45,0
19856	3 x 0,34	22	5,5	28,7	60,0
19857	4 x 0,34	22	5,8	35,7	76,0
19858	5 x 0,34	22	6,5	39,1	82,0
19859	7 x 0,34	22	7,2	52,7	110,0
19860	12 x 0,34	22	8,5	76,4	166,0
19861	18 x 0,34	22	10,0	99,7	216,0
19862	25 x 0,34	22	12,0	155,0	305,0
19863	36 x 0,34	22	13,0	188,0	340,0

Dimensions and specifications may be changed without prior notice. (RN05)