



Technical data

- halogen-free cross-linked control cable to DIN VDE 0282 part 13, HD 22.13 S1+A1
- **Temperature range**
flexing -5 °C to +70 °C
fixed installation -20 °C to +70 °C
- Permissible **operating temperature** at conductor +70C
- **Nominal voltage**
fixed installation U_0/U 06/1 kV
flexing U_0/U 450/750 V
- **Test voltage** 2500 V
- **Permanent tensile load**
max. 15 N/mm² under consideration of total copper cross-sections
- **Minimum bending radius**
for fixed installation 4x cable \varnothing
flexing 10x cable \varnothing

Cable structure

- Bare copper, fine wire stranded conductor to DIN VDE 0295 cl. 5, BS 6360 cl. 5, and IEC 60228 cl. 5 and HD 383
- Core insulation cross-linked, halogen-free, EI8 to DIN VDE 0282 part 1 (HD 22.1 S3)
- Core colours to DIN VDE 0293-308
- Cores stranded in layers with optimal lay-length
- Outer jacket, cross-linked halogen-free EM8 to DIN VDE 0282 part 1 (HD 22.1 S3)
- Sheath colour black

Properties

- **Test**
Behaviour in fire to EN 50265-2-1 (VDE 0472 part 804) and HD 405.3 cat. C
- Corrosiveness of combustion gases to EN 50267-2-2
Smoke density to HD 606
- Ozone resistant of single corethe insulation to EN 60811-2-1, HD 22.2

Note

- G = with green-yellow earth core;
x = without green-yellow earth core.
- AWG sizes are approximate equivalent values. The actual cross-section is in mm².

Application

Single and multicore sheathed cable, with low smoke and corrosive gas production in case of fire for interior use. Not suitable for continuous outside use. In this case, cable with a special tested covering should be used. Skin contact should be avoided when the cable is used in high temperatures.

CE = The product is conformed with the EC Low-Voltage Directive 2006/95/EG.

Part no.	No.cores x cross-sec. mm ²	Outer Ø min. - max. mm	Cop. weight kg / km	Weight approx. kg / km	AWG-No.
37176	1 x 1,5	5,7 - 7,1	14,4	58,0	16
37177	1 x 2,5	6,3 - 7,9	24,0	71,0	14
37178	1 x 4	7,2 - 9,0	38,0	100,0	12
37179	1 x 6	7,9 - 9,8	58,0	130,0	10
37180	1 x 10	9,5 - 11,9	96,0	230,0	8
37181	1 x 16	10,8 - 13,4	154,0	290,0	6
37182	1 x 25	12,7 - 15,8	240,0	420,0	4
37183	1 x 35	14,3 - 17,9	336,0	530,0	2
37184	1 x 50	16,5 - 20,6	480,0	750,0	1
37185	1 x 70	18,6 - 23,3	672,0	960,0	2/0
37186	1 x 95	20,8 - 26,0	912,0	1250,0	3/0
37187	1 x 120	22,8 - 28,6	1152,0	1560,0	4/0
37188	1 x 150	25,2 - 31,4	1440,0	1900,0	300 kcmil
37189	1 x 185	27,6 - 34,4	1776,0	2300,0	350 kcmil
37190	1 x 240	30,6 - 38,3	2304,0	2950,0	500 kcmil
37191	1 x 300	33,5 - 41,9	2880,0	3600,0	600 kcmil
37192	1 x 400	37,4 - 46,8	3840,0	4600,0	750 kcmil
37193	1 x 500	41,3 - 52,0	4800,0	6000,0	1000 kcmil
37194	2 x 1	7,7 - 10,0	19,0	95,0	17
37195	2 x 1,5	8,5 - 11,0	29,0	119,0	16
37196	2 x 2,5	10,2 - 13,1	48,0	172,0	14
37197	2 x 4	11,8 - 15,1	77,0	239,0	12
37198	2 x 6	13,1 - 16,8	115,0	319,0	10
37199	2 x 10	17,7 - 22,6	192,0	572,0	8
37200	2 x 16	20,2 - 25,7	307,0	767,0	6
37201	2 x 25	24,3 - 30,7	480,0	1154,0	4

Part no.	No.cores x cross-sec. mm ²	Outer Ø min. - max. mm	Cop. weight kg / km	Weight approx. kg / km	AWG-No.
37202	3 G 1	8,3 - 10,7	29,0	115,0	17
37203	3 G 1,5	9,2 - 11,9	43,0	144,0	16
37204	3 G 2,5	10,9 - 14,0	72,0	211,0	14
37205	3 G 4	12,7 - 16,2	115,0	290,0	12
37206	3 G 6	14,1 - 18,0	173,0	391,0	10
37207	3 G 10	19,1 - 24,2	288,0	706,0	8
37208	3 G 16	21,8 - 27,6	461,0	961,0	6
37209	3 G 25	26,1 - 33,0	720,0	1438,0	4
37210	3 G 35	29,3 - 37,1	1008,0	1814,0	2
37211	3 G 50	34,1 - 42,9	1440,0	2550,0	1
37212	3 G 70	38,4 - 48,3	2016,0	3210,0	2/0
37213	3 G 95	43,3 - 54,0	2736,0	4423,0	3/0
37214	3 G 120	47,4 - 60,0	3456,0	5405,0	4/0
37215	3 G 150	52,0 - 66,0	4320,0	6725,0	300 kcmil
37216	3 G 185	57,0 - 72,0	5328,0	8222,0	350 kcmil
37217	3 G 240	65,0 - 82,0	6192,0	10224,0	500 kcmil
37218	3 G 300	72,0 - 90,0	8640,0	12620,0	600 kcmil

Continuation ►