



## Technical data

- Harmonized welding cable with rubber jacket, according to DIN VDE 0282 part 6 or HD 22.6 S2
- **Conductor resistance** according to HD 383 cl. 6
- **Conductor resistance factor** at 20 °C - see Technical Informations
- **Temperature range** flexing -25 °C to +80 °C fixed installation -40 °C to +80 °C
- **Admissible working temperature** at conductor +85 °C
- **Nominal voltage**  $U_0/U$  100/100 V
- **Test voltage** 1000 V

## Cable structure

- Plain copper conductors (on request tinned conductor available), extra fine stranded to DIN VDE 0295, BS 6360, IEC 60228 and HD 383
- Separator over conductor
- Neoprene outer jacket, chlorinated rubber compound EM5
- Outer sheath black
- Without green-yellow marking

## Properties

- Test according to VDE 0482-332-1-2, DIN EN 60332-1-2/ IEC 60332-1 (equivalent DIN VDE 0472 part 804 test method B)
- Oil resistant to DIN EN 60811-2-1
- The cable also maintains its high flexibility under the effect of ozone, light, oxygen, inert gas, oil or petrol

## Note

- No. wires = Gauiding value, the number of individual wires are without obligation.

## Application

For use between the welding generator and the hand-electrode and the workpiece. For use in the automobile industry, in shipbuilding, in transport and conveyor systems, tool making machinery, welding robots etc. These cables retain their high flexibility even under influence of ozone, light, oxygen, protective gases, oil and petrol. The robust construction makes these cables resistant to both to cold and the heat as well as to flames. They are suitable for use in open spaces and in dry and damp conditions.

CE= The product is conformed with the EC Low-Voltage Directive 2006/95/EC.

### H01N2-D: Cables with standard flexibility, bending radius: approx. 12 x CableØ

Part no.	No. cores x cross-sec. mm <sup>2</sup>	No. wires x single wire Ø mm	Sheat Nominal value mm	Outer Ø min. - max. mm	Cop. weight kg / km	Weight approx. kg / km	AWG-No.
31001	1 x 10	320 x 0,2	2	7,7 - 9,7	96,0	135,0	8
31002	1 x 16	512 x 0,2	2	8,8 - 11,0	154,0	205,0	6
31003	1 x 25	800 x 0,2	2	10,1 - 12,7	240,0	302,0	4
31004	1 x 35	1120 x 0,2	2	11,4 - 14,2	336,0	420,0	2
31005	1 x 50	1600 x 0,2	2,2	13,2 - 16,5	480,0	586,0	1
31006	1 x 70	2240 x 0,2	2,4	15,3 - 19,2	672,0	798,0	2/0
31007	1 x 95	3024 x 0,2	2,6	17,1 - 21,4	912,0	1015,0	3/0
31008	1 x 120	614 x 0,5	2,8	19,2 - 24,0	1152,0	1310,0	4/0
31030	1 x 150	765 x 0,5	3	21,2 - 26,4	1440,0	1620,0	300 kcmil
31031	1 x 185	944 x 0,5	3,2	23,1 - 28,9	1776,0	1916,0	350 kcmil
31009	1 x 240	1225 x 0,5	3,4	25,0 - 29,5	2304,0	2540,0	500 kcmil

### H01N2-E: Cables with extreme high flexibility, bending radius: approx. 10 x CableØ

Part no.	No. cores x cross-sec. mm <sup>2</sup>	No. wires x single wire Ø mm	Sheat Nominal value mm	Outer Ø min. - max. mm	Cop. weight kg / km	Weight approx. kg / km	AWG-No.
31032	1 x 10	566 x 0,15	1,2	6,2 - 7,8	96,0	119,0	8
31033	1 x 16	903 x 0,15	1,2	7,3 - 9,1	154,0	181,0	6
31034	1 x 25	1407 x 0,15	1,2	8,6 - 10,8	240,0	270,0	4
31035	1 x 35	1974 x 0,15	1,2	9,8 - 12,3	336,0	363,0	2
31036	1 x 50	2830 x 0,15	1,5	11,9 - 14,8	480,0	528,0	1
31037	1 x 70	3952 x 0,15	1,5	13,6 - 17,0	672,0	716,0	2/0
31038	1 x 95	5370 x 0,15	1,8	15,6 - 19,5	912,0	1012,0	3/0
31039	1 x 120	3819 x 0,2	1,8	17,2 - 21,6	1152,0	1190,0	4/0
31019	1 x 150	4788 x 0,2	1,8	18,8 - 23,5	1440,0	1305,0	300 kcmil
31020	1 x 185	5852 x 0,2	1,8	20,4 - 25,5	1776,0	1511,0	350 kcmil

Dimensions and specifications may be changed without prior notice. (RK01)